



Accura[®] Xtreme[™]

Xtreme Class

Ultra tough grey plastic to replace CNC-machined polypropylene and ABS articles

Post-Cured Material

MEASUREMENT	CONDITION	METRIC	U.S.
Tensile Strength (MPa/PSI)	ASTM D 638	38-44	5510-6380
Tensile Modulus (MPa/KSI)	ASTM D 638	1790-1980	260-287
Elongation at Break (%)	ASTM D 638	14-22	14-22
Flexural Strength (MPa/PSI)	ASTM D 790	57-71	7540-10300
Flexural Modulus (MPa/KSI)	ASTM D 790	1520-2070	220-300
Impact Strength (J/m /Ft-lbs/in)	ASTM D 256	35-52	0.66-0.98
Heat Deflection Temperature	ASTM D 648 @ 66 PSI @ 264 PSI	62 °C 54 °C	144 °F 129 °F
Glass Transition (Tg)		70-74 °C	158-165 °F

Liquid Material

MEASUREMENT	CONDITION	VALUE
Viscosity	@ 30 °C (86 °F)	250-300 cps
Penetration Depth (Dp)		4.1 mils
Critical Exposure (Ec)		11.7 mJ/cm ²
Color		Grey
Solid Density	@ 25 °C (77 °F)	1.19 g/cm ³
Liquid Density	@ 25 °C (82 °F)	1.13 g/cm ³
Tested Build Styles		EXACT [™]

Features

- Tough and durable
- Resists breakage and handles challenging functional assemblies
- Great for snap fits, assemblies and demanding applications
- Ideal for master patterns for vacuum casting



www.3dsystems.com

UK
Tel: +44 1442 282 600
info@3dsystems-europe.com

**Germany, Scandinavia,
Eastern Europe, Middle East**
Tel: +49 6151 357 0
info@3dsystems-europe.com

USA
Tel: +1 803.326.3900
moreinfo@3dsystems.com

Asia-Pacific
Melbourne Tel: +61 3 9819 4422
Sydney Tel: +61 2 9516 5571
3dprinters.asiapac@3dsystems.com

Warranty/Disclaimer: The performance characteristics of these products may vary according to product application, operating conditions, or with end use. 3D Systems makes no warranties of any type, express or implied, including, but not limited to, the warranties of merchantability or fitness for a particular use.

© 2017 by 3D Systems, Inc. All rights reserved. Specifications subject to change without notice. Xtreme is a trademark, the 3D logo and Accura are registered trademarks of 3D Systems, Inc.