



Accura[®] 55

Rigid and strong plastic to stimulate and replace CNC-machined white ABS articles

Post-Cured Material

MEASUREMENT	CONDITION	METRIC	U.S.
Tensile Strength (MPa/PSI)	ASTM D 638	63-68	9200-9850
Tensile Modulus (MPa/KSI)	ASTM D 638	3200-3380	460-490
Elongation at Break (%)	ASTM D 638	5-8 %	5-8 %
Flexural Strength (MPa/PSI)	ASTM D 790	88-110	12830-15920
Flexural Modulus(MPa/KSI)	ASTM D 790	2690-3240	390-470
Impact Strength (J/m /Ft-lbs/in)	ASTM D 256 ASTM5420	12-22 1.1	0.2-0.4 0.81
Heat Deflection Temperature	ASTM D 648 @ 66 PSI @ 264 PSI	55-58 °C 51-53 °C	131-136 °F 123-127 °F
Coefficient of Thermal Expansion (CTE)	ASTM E 831-93 TMA (T<Tg, 0-40 °C) TMA (T<Tg, 75-140 °C)	61	141
		163	326
Glass Transition (Tg)	DMA, E''	56 °C	132 °F
Shore D		85	85

Features

- Rigid and strong
- Functional assemblies
- Short-run production parts

Liquid Material

MEASUREMENT	CONDITION	VALUE
Viscosity	@ 30 °C (86 °F)	155-185 cps
Penetration Depth (Dp)		5.2 mils
Critical Exposure (Ec)		7.4 mJ/cm ²
Color		White
Solid Density	@ 25 °C (77 °F)	1.20 g/cm ³ at 25 °C
Liquid Density	@ 25 °C (77 °F)	1.13 g/cm ³ at 25 °C



www.3dsystems.com

Warranty/Disclaimer: The performance characteristics of these products may vary according to product application, operating conditions, or with end use. 3D Systems makes no warranties of any type, express or implied, including, but not limited to, the warranties of merchantability or fitness for a particular use.

© 2017 by 3D Systems, Inc. All rights reserved. Specifications subject to change without notice. 3D Systems and Accura are registered trademarks and the 3D Systems logo is a trademark of 3D Systems, Inc.