

# ProJet<sup>®</sup> MJP 2500W

High throughput production of precision jewelry  
RealWax<sup>™</sup> patterns for metal casting



3D Systems' ProJet MJP 2500W Multijet 3D Printer quickly and consistently generates micro-detail, precision, 100% wax sacrificial metal casting patterns for high capacity jewelry production, without tooling time, cost or geometric limitations, delivering reliable and repeatable direct casting efficiency.

# Jewelry Wax Pattern Multijet Printing

## 3D printing solution for direct production of precision metal casting patterns

The ProJet MJP 2500W 3D printer employs Multijet Printing technology to consistently produce high fidelity, true-to-CAD wax sacrificial patterns, for precision investment casting for jewelry.

### GET MORE PATTERNS FASTER

Streamline your file-to-pattern workflow with the advanced 3D Sprint® software capabilities, fast and versatile MJP print speeds and batch support removal to deliver high quality, ready-to-cast patterns.

### RESULTS YOU CAN TRUST

Produce true-to-CAD patterns with exact, razor-sharp edge and fine feature definition for results you can rely on. Smooth surface and sidewall quality means less expensive hand work and a faster pattern-to-finished piece workflow. Visijet® M2 CAST 100% wax material melts like standard casting waxes, with negligible ash content for defect free castings.

### MANUFACTURING AGILITY

Multijet Printing provides more flexibility and throughput to develop your business and access the digital manufacturing world of customized pieces and series production. ProJet MJP 2500W jewelry printer makes production methods faster, easier and more effective, dramatically reducing lead times and costs.

### UNLOCK YOUR CREATIVITY

Increase geometric freedom without the limitations of hand crafting or tooling to create complex, precision patterns that cannot be made traditionally. MJP hands-free post-processing provides complete removal of supports from the tightest spaces without damaging fine feature details.

## The ProJet MJP 2500W

The ProJet MJP 2500W is an affordable 100% RealWax pattern 3D printer that adjusts to your workflow, delivering from several short run batches a day to next day for larger builds. These highly accurate, fine wax patterns are directly printed, without the time, costs and geometric limitations of tooling.

### HIGH THROUGHPUT

From fast short runs to high throughput, combine up to 10x faster print speeds and 3.7x larger build volume than similar class printers with rapid single lane printing for high productivity of 100% wax precision jewelry casting patterns with an affordable 3D printer. Improve the casting room efficiency and thereby the productivity, precision and possibilities of direct investment jewelry casting.

### HIGH QUALITY PATTERNS

Print sharp edges, extreme crisp details and smooth surfaces with high fidelity. The ProJet MJP 2500W printers is ideal for intricate precision jewelry pieces manufacturing with reduced metal hand polishing.

### EASE-OF-USE AND LOWER COSTS

Optimize part and labor costs with MJP ease-of-use, automated and efficient process—from file to finished direct casting pattern. With large volume capacity and 24/7 operation, the ProJet MJP 2500W printer allows fast amortization and a high return on your investment.



### JEWELRY / WATCH MANUFACTURING

Print crisp details on small features and micro-pave settings. Consistently achieve the highest level of precision and repeatability by adopting a digital foundry workflow for jewelry manufacturing.



### ART, FASHION AND COLLECTIBLES

Produce series or customized sculptures, figurines, replicas, collectibles and more without the constraint of tooling limitations. Our precision wax pattern 3D printer makes production methods faster, easier and more effective, dramatically reducing lead times.

# VisiJet® M2 CAST 100% Wax Material

## Best casting reliability

VisiJet M2 CAST is a 100% wax 3D printing material for the ProJet MJP 2500W printer, delivering durable, high quality patterns for reliable performance and results throughout existing lost-wax casting processes and equipment.



VisiJet M2 CAST melts like standard casting waxes, with negligible ash content for defect free castings.

It is durable for handling and casting fine features, and its high contrast deep purple color allows for easy fine details visualization.



## Sp 3D Sprint®

### End-to-end software solution for Multijet Printing workflows

Multijet Printers use 3D Sprint, 3D Systems' advanced software for file preparation, editing, printing and management from a single, intuitive interface. 3D Sprint enables the customer to significantly decrease cost of ownership of their 3D printers by reducing the need for costly software seats by third party vendors. A distinguishing feature of 3D Sprint software is its ease of use with automated part placement, support generation and tools to modify pattern geometry without the need to go back to a CAD program.

## Co 3D Connect™

### A new level of management in 3D production

3D Connect Service provides a secure cloud-based connection to 3D Systems service teams for proactive and preventative support to improve uptime and deliver production assurance for your system.

Properties	Condition	VisiJet M2 CAST	VisiJet M2 SUP
Composition		100% Wax	Wax Support Material
Color		Deep Purple	White
Bottle Quantity		1.17 kg	1.3 kg
Density @ 80 °C (liquid)	ASTM D3505	0.80 g/cm <sup>3</sup>	0.87 g/cm <sup>3</sup>
Melting Point		61-66 °C	55-65 °C
Softening Point		40-48 °C	N/A
Volumetric Shrinkage, from 40 °C to RT		2 %	N/A
Linear Shrinkage, from 40 °C to RT		0.70 %	N/A
Needle Penetration Hardness	ASTM D1321	12	N/A
Ash Content	ASTM 2584	< 0.05 %	N/A
Description		High resolution, durable casting wax	Eco friendly, hands-free dissolvable wax

\* DISCLAIMER: It is the responsibility of each customer to determine that its use of any VisiJet material is safe, lawful and technically suitable to the customer's intended applications. The values presented here are for reference only and may vary. Customers should conduct their own testing to ensure suitability for their intended application.

# Projet® MJP 2500W

High throughput production of precision jewelry RealWax™ patterns for metal casting

PRINTER HARDWARE	
<b>Dimensions (WxDxH)</b>	
3D Printer Crated	1397 x 927 x 1314 mm (55 x 36.5 x 51.7 in)
3D Printer Uncrated	1120 x 740 x 1070 mm (44.1 x 29.1 x 42.1 in)
<b>Weight</b>	
3D Printer Crated	325 kg (716 lb)
3D Printer Uncrated	211 kg (465 lb)
<b>Electrical</b>	100-127 VAC, 50/60 Hz, single-phase, 15A 200-240 VAC, 50 Hz, single-phase, 10A Single C14 receptacle
<b>Operating Temperature Range</b>	18-28 °C (64-82 °F), reduced print speed at > 25 °C (77 °F)
<b>Operating Humidity</b>	30-70 % relative humidity
<b>Noise</b>	< 65 dBA estimated (at medium fan setting)
<b>Certifications</b>	CE

PRINTING SPECIFICATIONS	
<b>Printing Mode</b>	XHD - Xtreme High Definition
<b>Net Build Volume (xyz)<sup>1</sup></b>	294 x 211 x 144 mm (11.6 x 8.3 x 5.6 in)
<b>Resolution (xyz)</b>	1200 x 1200 x 1600 DPI; 16 µ layers
<b>Accuracy (typical)<sup>2</sup></b>	±0.0508 mm/25.4 mm (±0.002 in/in) of part dimension typical for any single printer ±0.1016 mm/25.4 mm (±0.004 in/in) of part dimension across printer population

<sup>1</sup> Maximum part size is dependent on geometry, among other factors.

<sup>2</sup> Accuracy may vary depending on build parameters, part geometry and size, part orientation, and post-processing.

<sup>3</sup> For Windows 10, make sure you have applied the most recent Windows updates for the application to run correctly.

MATERIALS	
<b>Build Material</b>	Visijet M2 CAST
<b>Support Material</b>	Visijet M2 SUW
<b>Material Packaging</b>	
Build Material	In clean 1.17 kg (2.58 lbs) bottles (printer holds up to 2 with auto-switching)
Support Material	In clean 1.3 kg (2.87 lbs) bottles (printer holds up to 2 with auto-switching)

SOFTWARE AND NETWORK	
<b>3D Sprint® Software</b>	Easy build job set-up, submission and job queue management; Automatic part placement and build optimization tools; Part stacking and nesting capability; Extensive part editing tools; Automatic support generation; Job statistics reporting tools
<b>3D Connect™ Capable</b>	3D Connect Service provides a secure cloud-based connection to 3D Systems service teams for support.
<b>E-mail Notice Capability</b>	Yes
<b>Internal Hard Drive Capacity</b>	500 Gb minimum
<b>Connectivity</b>	Network ready with 10/100/1000 base ethernet interface; USB port
<b>Client Operating System</b>	Windows® 7, Windows 8 or Windows 8.1 (Service Pack), Windows 10 <sup>3</sup>
<b>Input Data File Formats Supported</b>	STL, CTL, OBJ, PLY, ZPR, ZBD, AMF, WRL, 3DS, FBX, IGES, IGS, STEP, STP, MJPDDD

Warranty/Disclaimer: The performance characteristics of these products may vary according to product application, operating conditions, material combined with, or with end use. 3D Systems makes no warranties of any type, express or implied, including, but not limited to, the warranties of merchantability or fitness for a particular use.

© 2020 by 3D Systems, Inc. All rights reserved. Specifications subject to change without notice. 3D Systems, the 3D Systems logo, Projet, Visijet and 3D Sprint are registered trademarks and RealWax is a trademark of 3D Systems, Inc.