




3D Sprint



Feature

Feature	SLA	Figure 4	NextDent	SLS	MJP
Easy Printer Configuration	•	•	•	•	•
Save & Load Printer Configurations	•	•	•	•	•
Consolidate Parts for Printing	•	•	•	•	•
Noise Surface Texturing	•	•	•	•	•
Advanced Fix Tools	•	•	•	•	•
Cylinder Cut & Precise Position of Cut Plane, Edit Split Line	•	•	•	•	•
Custom Parameters in Quality Check	•	•	•	•	•
Import latest CAD formats	•	•	•	•	•
Wall Thickness Measurement	•	•	•	•	•
UI/UX Improvements	•	•	•	•	•
Trapped Volume Check	•	•	•		
Stilts for Additional Support	•	•	•		
Anchor Points in Closed Regions and based on Face Angle	•	•	•		
Edge & Polyline Based Anchor Points	•	•	•		
Local Reinforcement of Supports	•				
Robust Support Structures	•				
Accuracy Wizard	•				
Advanced Auto-Placement	•				
QuickCast Diamond	•				
Early Model Support (available as an add-on)	•				
Uniform Scan Time/Cross-Sectional Area and Interlock Check during Auto-Placement				•	
User-defined cage				•	
Hollow Dental Models			•		
Support Posteriors on Stacked Arches			•		
Simple or Advanced UI Menus			•		
Struts (for Figure 4 Jewelry)					
(Other Figure 4 printers already have struts inv3D Sprint 3.0.)					

Get In Touch

Contact us for a demo at hello@oqton.com

